

Network Camera Firmware Version: V5.5.114

Release Note

(2021-05-24)

Firmware Basic Information	Firmware Version: V5.5.114 build210428
---------------------------------------	--

2xx3G2, 2xx6G2, 2xx7G2, 3xx3G2, 3xx6G2, 3xx7G2 Camera V5.5.114

Features

1. New Features

- Newly release 2x47G2 models which support separate flash alarm linkage.

2. Improved Features

- Optimize the image effect of 2xx3G2 devices.
- Solve the issue that the device cannot be started with a low probability after upgrading to V5.5.113 version.
- Optimize the problem of obvious abnormal vertical lines on the image in a jittery environment.

Customer Impact and Recommended Action

This update refers to function/compatibility improvement and will take effect automatically after the Date of Change. We are very sorry for any inconvenience of use-habit changes caused by this action. For any questions and request for this firmware, please contact our local technical support team.

Remarks:

- Hikvision reserves the right to change, alter or withdraw the above notification without prior notice.
- Product design and specifications are subject to change without prior notice.
- The Hikvision firmware may contain errors known as errata which may cause the product to deviate from published specifications. Current characterized errata are available on request.
- Hikvision is not liable for any typing or printing errors.

Hikvision Digital Technology CO., Ltd.

No. 555 Qianmo Road, Binjiang District, Hangzhou
310051, China

Tel: +86-571-8807-5998

Supported Product List (1x83G0, 2xx3G2, 2xx6G2(C), 2xx7G2(C), 3xx3G2, 3xx6G2(C), 3xx7G2(C) Series)	
Product Category	Model Number
1 Series	DS-2CD1083G0-I(U)(F)
1 Series	DS-2CD1183G0-I(U)(F)
1 Series	DS-2CD1383G0-I(U)(F)
Pro Series	DS-2CD2023G2-I(U)
Pro Series	DS-2CD2043G2-I(U)
Pro Series	DS-2CD2123G2-I(S)
Pro Series	DS-2CD2123G2-IU
Pro Series	DS-2CD2143G2-I(S)
Pro Series	DS-2CD2143G2-IU
Pro Series	DS-2CD2323G2-I(U)
Pro Series	DS-2CD2343G2-I(U)
Pro Series	DS-2CD2423G2-I
Pro Series	DS-2CD2443G2-I
Pro Series	DS-2CD2623G2-IZS
Pro Series	DS-2CD2643G2-IZS
Pro Series	DS-2CD2723G2-IZS
Pro Series	DS-2CD2743G2-IZS
Pro Series	DS-2CD2H23G2-IZS
Pro Series	DS-2CD2H43G2-IZS
Pro Series	DS-2CD2T23G2-2I/4I

Pro Series	DS-2CD2T43G2-2I/4I
Pro/2 Series with AcuSense	DS-2CD2026G2-I(U)(C)
Pro/2 Series with AcuSense	DS-2CD2026G2-IU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2046G2-I(U)(C)
Pro/2 Series with AcuSense	DS-2CD2046G2-IU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2126G2-I(SU)(C)
Pro/2 Series with AcuSense	DS-2CD2146G2-I(SU)(C)
Pro/2 Series with AcuSense	DS-2CD2326G2-I(U)(C)
Pro/2 Series with AcuSense	DS-2CD2326G2-ISU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2346G2-I(U)(C)
Pro/2 Series with AcuSense	DS-2CD2346G2-ISU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2426G2-I(C)
Pro/2 Series with AcuSense	DS-2CD2446G2-I(C)
Pro/2 Series with AcuSense	DS-2CD2626G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2626G2-IZSU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2646G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2646G2-IZSU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2726G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2746G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2H26G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2H46G2(T)-IZS(C)
Pro/2 Series with AcuSense	DS-2CD2T26G2-2I/4I(C)
Pro/2 Series with AcuSense	DS-2CD2T26G2-ISU/SL(C)
Pro/2 Series with AcuSense	DS-2CD2T46G2-2I/4I(C)
Pro/2 Series with AcuSense	DS-2CD2T46G2-ISU/SL(C)
Pro/2 Series with ColorVu	DS-2CD2027G2-L(U)(C)
Pro/2 Series with ColorVu	DS-2CD2047G2-L(U)(C)

Pro/2 Series with ColorVu	DS-2CD2047G2-LU/SL(C)
Pro/2 Series with ColorVu	DS-2CD2127G2(-SU)(C)
Pro/2 Series with ColorVu	DS-2CD2147G2(-SU)(C)
Pro/2 Series with ColorVu	DS-2CD2327G2-L(U)(C)
Pro/2 Series with ColorVu	DS-2CD2347G2-L(U)(C)
Pro/2 Series with ColorVu	DS-2CD2347G2-LSU/SL(C)
Pro/2 Series with ColorVu	DS-2CD2647G2-LZS(C)
Pro/2 Series with ColorVu	DS-2CD2747G2-LZS(C)
Pro/2 Series with ColorVu	DS-2CD2T27G2-L(C)
Pro/2 Series with ColorVu	DS-2CD2T47G2-L(C)
Pro/2 Series with ColorVu	DS-2CD2T47G2-LSU/SL(C)
Pro/3 Series with AcuSense	DS-2CD3026G2-IS(C)
Pro/3 Series with AcuSense	DS-2CD3026G2-IU/SL(C)
Pro/3 Series with AcuSense	DS-2CD3056G2-IS(C)
Pro/3 Series with AcuSense	DS-2CD3056G2-IU/SL(C)
Pro/3 Series with AcuSense	DS-2CD3126G2-IS(U)(C)
Pro/3 Series with AcuSense	DS-2CD3156G2-IS(U)(C)
Pro/3 Series with AcuSense	DS-2CD3326G2-IS(U)(C)
Pro/3 Series with AcuSense	DS-2CD3326G2-ISU/SL(C)
Pro/3 Series with AcuSense	DS-2CD3356G2-IS(U)(C)
Pro/3 Series with AcuSense	DS-2CD3356G2-ISU/SL(C)
Pro/3 Series with AcuSense	DS-2CD3626G2(T)-IZS(C)
Pro/3 Series with AcuSense	DS-2CD3656G2(T)-IZS(C)
Pro/3 Series with AcuSense	DS-2CD3726G2(T)-IZS(C)
Pro/3 Series with AcuSense	DS-2CD3756G2(T)-IZS(C)
Pro/3 Series with AcuSense	DS-2CD3B26G2T-IZHSY(C)
Pro/3 Series with AcuSense	DS-2CD3B46G2T-IZHSY(C)

Pro/3 Series with AcuSense	DS-2CD3H26G2-IZS(C)
Pro/3 Series with AcuSense	DS-2CD3H56G2-IZS(C)
Pro/3 Series with AcuSense	DS-2CD3T26G2-4IS(C)
Pro/3 Series with AcuSense	DS-2CD3T26G2-ISU/SL(C)
Pro/3 Series with AcuSense	DS-2CD3T56G2-4IS(C)
Pro/3 Series with AcuSense	DS-2CD3T56G2-ISU/SL(C)
Pro/3 Series with ColorVu	DS-2CD3047G2-LS(U)(C)
Pro/3 Series with ColorVu	DS-2CD3347G2-LS(U)(C)
Pro/3 Series with ColorVu	DS-2CD3647G2-LZS(C)
Pro/3 Series with ColorVu	DS-2CD3747G2-LZS(C)

Note: Models in red font are newly released models.